



Stingray F-146

- Versatile 1.4 MP camera
- Advanced feature set
- Many variants
- Excellent image quality

Description

Digital machine vision camera - FireWire - Sony ICX267

The Stingray F-146B/F-146C is equipped with a Sony HAD CCD sensor (ICX267). At full resolution, this digital machine vision camera runs at 15 frames per second. Higher frame rates can be reached by using a smaller area of interest (AOI), binning (b/w) or sub-sampling.

Options:


- IEEE 1394b connectors: 2 x copper (daisy chain), Hirose power: out
- Various IR cut/pass filters, various lens mounts
- Angled head, board level version, white medical housing

Specifications

Stingray	F-146	
Interface	IEEE 1394b - 800 Mb/s, 2 ports, daisy chain	
Resolution	1388 (H) × 1038 (V)	
Sensor	Sony ICX267	
Sensor type	CCD Progressive	
Sensor size	Type 1/2	
Pixel size	4.65 μm x 4.65 μm	
Lens mount (default)	C-Mount	
Max. frame rate at full resolution	15 fps	
ADC	14 bit	
Image buffer (RAM)	Up to 128 MByte	
Output		



Stingray	F-146	
Bit depth	8-14 bit	
Monochrome pixel formats	Mono8, Mono12, Mono16	
RGB color pixel formats	RGB8	
Raw pixel formats	Raw8, Raw12, Raw16	
General purpose inputs/outputs (GPIOs)		
Opto-isolated I/Os	2 inputs, 4 outputs	
RS232	1	
Operating conditions/dimensions		
Operating temperature	+5 °C to +45 °C	
Power requirements (DC)	8 V to 36 V	
Power consumption	<4 W (@ 12 VDC)	
Mass	92 g	
Body dimensions (L × W × H in mm)	72.9 × 44 × 29 (including connectors)	
Regulations	CE: 2014/30/EU (EMC), 2011/65/EU (RoHS); FCC Class B	



Features

- High SNR mode (up to 24 dB better signal-to-noise ratio)
- Low-noise binning mode
- Shading correction
- Defect pixel correction
- Area of interest (AOI), separate AOI for auto features



- Binning
- Decimation
- Auto gain (manual gain control: 0 to 24.4 dB)
- Auto exposure (39 µs to 67 s)
- Auto white balance
- Look-up table (LUT)
- Hue, saturation
- Color correction
- Local color anti-aliasing
- Reverse X/Y
- Deferred image transport
- Trigger programmable, level, single, bulk, programmable delay
- Sequence mode (changes the camera settings on the fly)
- SIS (secure image signature, time stamp for trigger, frame count etc.)
- Storable user sets


Scope of delivery


• Camera and IEEE 1394b cable (other configurations on request)




Technical drawing

2 x 1394b copper









Applications

The Stingray F-146B/F-146C digital machine vision cameras fit many applications, their flexibility is a benefit of all Stingray FireWire cameras. Allied Vision recommends using this camera for:

- Industrial inspection and automation
- Logistics
- Science and research
- Healthcare and medical (white housing available)
- Multimedia, entertainment and sports
- Intelligent traffic solutions (ITS)

Additionally, it is ideally suited for:

- Demanding OEM camera applications (board level versions with separate sensor board available on request)
- Daisy chain applications (two copper connectors)